

## DECTO G, receiver with holder

### Universal receiver with acoustic sound signal

Product number :16829000



#### Topfeatures

- Ideal for interior finishing, can also be used outdoors.
- Receiver Decto for red laser beams.

#### All special features at a glance

- Receiver has integrated horizontal and vertical bubble to align the receiver quickly and precisely.
- Simple operation.
- Reading of the laser beam display possible on the front as well as on the rear side
- Acoustic sound signal and LED display indicate in which direction the laser beam must be moved.
- Sound signal can be switched off.

#### Description

The NESTLE DECTO-G laser receiver is suitable for all pulsating line lasers with green laser light. Thanks to the integrated bubble level, the receiver can be aligned quickly and precisely. An acoustic sound signal and the LED display indicate in which direction the receiver must be moved. The sound signal is optional and can be switched off. The receiver is best suited for indoor use, but can also be ideally used outdoors.

#### Technical Details

Working range	depending on the laser instrument
Auto. Shutdown	10 min
Batteries	DC 9 V
Reception area	35 mm
Accuracy	± 0.5 - 1 (depending on distance) mm
Weight	200 g
Dimensions	149 x 54 x 24 mm

#### Scope of supply

DECTO receiver, Bracket